



## Boats for the VACO 250

CMi Reference	Description	Type
1800	(10) Large W boats for VACO 250	<p>Tungsten Boat 260W 120A 0.1 mm</p> 
1801	(10) Small W boats for VACO 250	<p>Tungsten Boat 260W 100A 0.1 mm</p> 

## Materials for the VACO 250

CMi Reference	Material	Quantity
4901	Au : Gold grains	6 grammes
4902	Ag : Silver granulate	around 4 grammes
4903	Al : Aluminum rods	around 8 grammes
4904	Cr : Chromium granulate	around 10 grammes
4905	Cu : Copper rods	around 20 grammes
4906	In : Indium rods	around 25 grammes
1504	Precision tweezers (stainless steel) FC-SA	