

Measure Reference	Machine	Recipe	Adh. Layer	Film	Results	+/- %	Substrates	Measurement Tool	number of sites	Date	User
050	EVA760	250_Cr_160	-	Cr	192 nm	6.1	Float glass	DekTak	5	21.10.2014	bellenrieder
					6.2352 Ω /sq	5.2	Float glass	OmniMap RS-75	21		
					775 MPa	-	Si Test	FLX 2320-S	1		
051	EVA760	250_Cr-Au_160-160	Cr 100Å	Au	180 nm	2.5	Float glass	DekTak	5	27.10.2014	bellenrieder
					0.1504 Ω /sq	1.7	Float glass	OmniMap RS-75	21		
					176 MPa	-	Si Test	FLX 2320-S	1		
052	EVA760	250_Cr-Al_160-160	Cr 100Å	Al	176 nm	3.8	Float glass	DekTak	5	27.10.2014	bellenrieder
					0.2036 Ω /sq	5.4	Float glass	OmniMap RS-75	21		
					163 MPa	-	Si Test	FLX 2320-S	1		
053	EVA760	250_Ti_160	-	Ti	180 nm	7.0	Float glass	DekTak	5	27.10.2014	bellenrieder
					4.8666 Ω /sq	8.9	Float glass	OmniMap RS-75	21		
					-178 MPa	-	Si Test	FLX 2320-S	1		
054	EVA760	350_Cr_80	-	Cr	181 nm	2.0	Float glass	DekTak	5	03.11.2014	bellenrieder
					4.9442 Ω /sq	2.7	Float glass	OmniMap RS-75	21		
					1,008 MPa	-	Si Test	FLX 2320-S	1		
055	EVA760	350_Cr-Au_80-80	Cr 100Å	Au	183 nm	2.0	Float glass	DekTak	5	03.11.2014	bellenrieder
					0.1386 Ω /sq	2.4	Float glass	OmniMap RS-75	21		
					194 MPa	-	Si Test	FLX 2320-S	1		
056	EVA760	350_Cr-Al_80-80	Cr 100Å	Al	201 nm	5.5	Float glass	DekTak	5	03.11.2014	bellenrieder
					0.1901 Ω /sq	1.7	Float glass	OmniMap RS-75	21		
					151 MPa	-	Si Test	FLX 2320-S	1		
057	EVA760	350_Ti_80	-	Ti	191 nm	4.5	Float glass	DekTak	5	03.11.2014	bellenrieder
					4.6075 Ω /sq	5.7	Float glass	OmniMap RS-75	21		
					-115 MPa	-	Si Test	FLX 2320-S	1		
058	EVA760	450_Cr_50	-	Cr	179 nm	4.8	Float glass	DekTak	5	10.11.2014	bellenrieder
					5.8828 Ω /sq	3.9	Float glass	OmniMap RS-75	21		
					1,010 MPa	-	Si Test	FLX 2320-S	1		
059	EVA760	450_Cr-Au_50-50	Cr 100Å	Au	191 nm	2.5	Float glass	DekTak	5	10.11.2014	bellenrieder
					0.1341 Ω /sq	1.1	Float glass	OmniMap RS-75	21		
					178 MPa	-	Si Test	FLX 2320-S	1		
060	EVA760	450_Cr-Al_50-50	Cr 100Å	Al	205 nm	4.3	Float glass	DekTak	5	10.11.2014	bellenrieder
					0.2307 Ω /sq	6.4	Float glass	OmniMap RS-75	21		
					MPa	-	Si Test	FLX 2320-S	1		
061	EVA760	450_Ti_50		Ti	199 nm	3.9	Float glass	DekTak	5	10.11.2014	bellenrieder
					5.1848 Ω /sq	4.5	Float glass	OmniMap RS-75	21		
					61 MPa	-	Si Test	FLX 2320-S	1		
062	EVA760	250_Cr-Pt_160-160	Cr 200Å	Pt	210 nm	3.8	Float glass	DekTak	5	21.01.2015	planglet gclerc
					0.6228 Ω /sq	2.0	Si+SiN	OmniMap RS-75	5		
					654 MPa	0.7	Si Test	FLX 2320-S	2		

Measure Reference	Machine	Recipe	Adh. Layer	Film	Results	+/- %	Substrates	Measurement Tool	number of sites	Date	User
063	EVA760	350_Cr-Pt_80-80	Cr 100Å	Pt	200 nm 0.6882 Ω/sq 467 MPa	3.3 1.9 0.8	Float glass Si+SiN Si Test	DekTak OmniMap RS-75 FLX 2320-S	5 5 2	21.01.2015	planglet gclerc
064	EVA760	450_Cr-Pt_50-50	Cr 100Å	Pt	200 nm 0.6602 Ω/sq 340 MPa	1.9 1.2 0.1	Float glass Si+SiN Si Test	DekTak OmniMap RS-75 FLX 2320-S	5 5 2	21.01.2015	planglet gclerc
065	EVA760	250_Cr-Cu_160-160	Cr 100Å	Cu	250 nm 0.0873 Ω/sq 155 MPa	15.7 13.1 0.1	Float glass Si+SiN Si Test	DekTak OmniMap RS-75 FLX 2320-S	5 5 2	12.02.2015	planglet gclerc
066	EVA760	350_Cr-Cu_80-80	Cr 100Å	Cu	229 nm 0.1033 Ω/sq 189 MPa	4.0 4.6 0.1	Float glass Si+SiN Si Test	DekTak OmniMap RS-75 FLX 2320-S	5 5 2	12.02.2015	planglet gclerc
067	EVA760	450_Cr-Cu_50-50	Cr 100Å	Cu	219 nm 0.1087 Ω/sq 183 MPa	2.9 3.2 0.1	Float glass Si+SiN Si Test	DekTak OmniMap RS-75 FLX 2320-S	5 5 2	12.02.2015	planglet gclerc
068	EVA760	450_Cr-Ni_50-50	Cr 200Å	Ni	158 nm Ω/sq MPa	2.3	Float glass	DekTak	5	19.12.2016	gclerc
069	EVA760	250_Cr-Co_160	Cr 100Å	Co	202 nm 0.5875 Ω/sq 933 MPa	5.4 6.7	Float glass Si+SiN Si Test	DekTak OmniMap RS-75 FLX 2320-S	5 5 1	14.12.2017	rjuttin planglet gclerc
070	EVA760	350_Cr-Co_80	Cr 100Å	Co	215 nm 0.5540 Ω/sq 1,002 MPa	5.2 4.8	Float glass Si+SiN Si Test	DekTak OmniMap RS-75 FLX 2320-S	5 5 1	14.12.2017	rjuttin planglet gclerc
071	EVA760	450_Cr-Co_50	Cr 100Å	Co	312 nm 0.3653 Ω/sq 1,002 MPa	2.2 2.5	Float glass Si+SiN Si Test	DekTak OmniMap RS-75 FLX 2320-S	5 5 1	14.12.2017	rjuttin planglet gclerc
072	EVA760	450_Cr-Ag_50	Cr 100Å	Ag	187 nm 0.1210 Ω/sq 122 MPa	3.0 1.1 4.3	Float glass Float glass Si Test	DekTak OmniMap RS-75 FLX 2320-S	5 5 2	19.02.2020	rjuttin
073	EVA760	350_Cr-Ag_80	Cr 100Å	Ag	158 nm 0.1468 Ω/sq 147 MPa	3.7 2.0 3.8	Float glass Float glass Si Test	DekTak OmniMap RS-75 FLX 2320-S	5 5 2	19.02.2020	rjuttin
074	EVA760	250_Cr-Ag_160	Cr 100Å	Ag	144 nm 0.1636 Ω/sq 147 MPa	5.5 5.6 3.8	Float glass Float glass Si Test	DekTak OmniMap RS-75 FLX 2320-S	5 5 2	19.02.2020	rjuttin